Diesel generator set QSK23 series engine



> Specification sheet 545 kW - 800 kW 60Hz 500 kW - 720 kW 50 Hz

Our energy working for you.™



Description

Cummins Power Generation commercial generator sets are fully integrated power generation systems providing optimum performance, reliability and versatility for stationary standby and prime power applications. Codes may not be available with all model configurations – consult factory for availability.



This generator set is designed in facilities certified to ISO 9001 and manufactured in facilities certified to ISO 9001 or ISO 9002.



The Prototype Test Support (PTS) program verifies the performance integrity of the generator set design. Cummins Power Generation products bearing the PTS symbol meet the prototype test requirements of NFPA 110 for Level 1 systems.



All low voltage models are CSA certified to product class 4215-01.



The generator set is available listed to UL 2200, Stationary Engine Generator Assemblies for all 60 Hz low voltage models. The PowerCommand control is Listed to UL 508 - Category NITW7 for U.S. and Canadian usage. Circuit breaker assemblies are UL 489 Listed for 100% continuous operation and also UL 869A Listed Service Equipment.

Features

Cummins® heavy-duty engine - Rugged 4-cycle, industrial diesel delivers reliable power, low emissions and fast response to load changes.

Alternator - Several alternator sizes offer selectable motor starting capability with low reactance 2/3 pitch windings, low waveform distortion with non-linear loads and fault clearing short-circuit capability.

Permanent magnet generator (PMG) - Offers enhanced motor starting and fault clearing short-circuit capability.

Control system - The PowerCommand[®] electronic control is standard equipment and provides total genset system integration including automatic remote starting/stopping, precise frequency and voltage regulation, alarm and status message display, AmpSentry[™] protection, output metering, auto-shutdown at fault detection and NFPA 110 Level 1 compliance.

Cooling system - Standard integral set-mounted radiator system, designed and tested for rated ambient temperatures, simplifies facility design requirements for rejected heat.

Enclosures - Optional weather protective and sound attenuated enclosures are available.

NFPA - The genset accepts full rated load in a single step in accordance with NFPA 110 for Level 1 systems.

Warranty and service - Backed by a comprehensive warranty and worldwide distributor network.

	Standby rating		Prime rating		Continuous rating		Data sheets	
	60 Hz	50 Hz	60 Hz	50 Hz	60 Hz	50 Hz		
Model	kW (kVA)	kW (kVA)	kW (kVA)	kW (kVA)	kW (kVA)	kW (kVA)	60 Hz	50 Hz
DQCA	600 (750)	545 (681)	545 (681)	500 (625)			D-3316	D-3319
DQCB	750 (938)	660 (825)	680 (850)	600 (750)			D-3317	D-3320
DQCC	800 (1000)	720 (900)	725 (906)	656 (820)			D-3318	D-3321

Generator set specifications

Governor regulation class	ISO8528 Part 1 Class G3		
Voltage regulation, no load to full load	± 0.5%		
Random voltage variation	± 0.5%		
Frequency regulation	Isochronous		
Random frequency variation	± 0.25%		
Radio frequency emissions compliance	IEC 801.2 through IEC 801.5; MIL STD 461C, Part 9		

Engine specifications

Bore	169.9 mm (6.69 in)			
Stroke	169.9 mm (6.69 in)			
Displacement	23.15 litres (1413 in³)			
Configuration	Cast iron, in line 6 cylinder			
Battery capacity	1400 amps minimum at ambient temperature of 0 °C to 10 °C (32 °F to 50 °F)			
Battery charging alternator	35 amps			
Starting voltage	24 volt, negative ground			
Fuel system	Direct injection: number 2 diesel fuel, fuel filter, automatic electric fuel shutoff			
Fuel filter	Spin-on fuel filter with water separator			
Air cleaner type	Dry replaceable element with restriction indicator			
Lube oil filter type(s)	Fleetguard dual venturi spin-on, combination full flow and bypass filters			
Standard cooling system	High ambient radiator			

Alternator specifications

Design	Brushless, 4 pole, drip proof revolving field
Stator	2/3 pitch
Rotor	Single bearing, flexible discs
Insulation system	Class H
Standard temperature rise	125 °C standby at 40 °C ambient
Exciter type	PMG (permanent magnet generator)
Phase rotation	A (U), B (V), C (W)
Alternator cooling	Direct drive centrifugal blower fan
AC waveform total harmonic distortion	< 5% no load to full linear load, < 3% for any single harmonic
Telephone influence factor (TIF)	< 50 per NEMA MG1-22.43
Telephone harmonic factor (THF)	< 3

Available voltages

60 Hz line-neutral/line-line				50 Hz line-	50 Hz line-neutral/line-line			
• 110/190	• 127/220	• 230/380	• 277/480	• 110/190	• 120/208	• 220/380	• 240/416	
• 115/200	• 139/240	• 240/416	• 347/600	• 115/200	127/220	• 230/400	• 255/440	
• 120/208	• 220/380	• 255/440						

^{*} Note: Consult factory for other voltages.


Generator set options and accessories

Engine □ 208/240/480 V coolant heater for ambient above 4.5 °C (40 °F) □ Fuel/water separator □ Heavy duty air cleaner	Alternator □ 80 °C rise □ 105 °C rise □ 125 °C rise □ 120/240 V anti-condensation heater □ Temperature sensor – alternator	Exhaust system ☐ Industrial grade exhaust silencer ☐ Residential grade exhaust silencer ☐ Critical grade exhaust	 □ Battery rack with hold-down - floor standing □ Circuit breaker - set mounted □ Disconnect switch - set mounted □ PowerCommand Network 		
Control panel ☐ 120/240 V 100 W control anti-condensation heater ☐ Paralleling configuration ☐ Remote fault signal package ☐ Run relay package	bearing RTD Cooling system □ 50 °C ambient	silencer Generator set □ AC entrance box □ Battery	 ☐ Remote annunciator panel ☐ Spring isolators ☐ 2 year warranty ☐ 5 year warranty ☐ 10 year major components warranty 		

^{*} Note: Some options may not be available on all models - consult factory for availability.

Our energy working for you.™

www.cumminspower.com





Control system PCC 3201



PowerCommand control is an integrated generator set control system providing governing, voltage regulation, engine protection and operator interface functions. Major features include:

- Integral AmpSentry[™] Protective Relay providing a full range of alternator protection functions that are matched to the alternator provided.
- Battery monitoring and testing features and smart starting control system.
- Three phase sensing, full wave rectified voltage regulation system, with a PWM output for stable operation with all load types.
- Control suitable for operation in ambient temperatures from -40 °C to +70 °C (-40 °F to +158 °F) and altitudes to 5000 meters (13,000 feet).
- Prototype tested; UL, CSA, and CE compliant.
- InPower PC-based service tool available for detailed diagnostics.
- Optional Echelon® LONWORKS® network interface.

Operator/display panel

- Off/manual/auto mode switch
- Manual run/stop switch
- Panel lamp test switch
- Emergency stop switch
- Exercise switch
- Alpha-numeric display with pushbutton access for viewing engine and alternator data and providing setup, controls and adjustments
- LED lamps indicating not in auto, common warning, common shutdown, remote start
- Configurable for local language

Engine protection

- Overspeed shut down
- Low oil pressure warning and shut down
- High coolant temperature warning and shut down
- High oil temperature warning
- Low coolant level warning or shut down
- Low coolant temperature warning
- High and low battery voltage warning
- Weak battery warning
- Dead battery shut down
- Fail to start (overcrank) shut down
- Fail to crank shut down
- Redundant start disconnect
- Cranking lockout
- Sensor failure indication

Engine data

- DC voltage
- Lube oil pressure
- Coolant temperature
- Lube oil temperature
- Engine speed
- Engine ECM data

AmpSentry AC protection

- Over current and short-circuit shut down
- Over current warning
- Single and three phase fault regulation
- Over and under voltage shut down
- Over and under frequency shut down
- Overload warning with alarm contact
- Reverse power and reverse Var shut down

Alternator data

- Line-to-line and line-to-neutral AC volts
- Three phase AC current
- Frequency
- Total and individual phase power factor, kW and kVA
- Bus voltage and frequency (with paralleling options)

Other data

- Genset model data
- Start attempts, starts, running hours
- kW hours (total and since reset)
- Fault history
- Load profile (accessible with InPower)

Governing

- Digital electronic isochronous governor
- Temperature dynamic governing
- Smart idle speed mode

Voltage regulation

- Digital PWM electronic voltage regulation
- Three phase line-to-neutral sensing
- Single and three phase fault regulation
- Configurable torque matching

Control functions

- Data logging on faults
- Fault simulation (requires InPower)
- Time delay start and cooldown
- Cycle cranking
- Configurable customer outputs (4)
- Configurable network inputs (8) and outputs (16) (with optional network)
- Remote emergency stop

Paralleling (Option)

- Active digital phase lock loop synchronizer
- Isochronous kW and kVar load sharing controls
- kW import/export and kVar/PF control for utility (mains) paralleling

Options

☐ Thermostatically controlled space heater	
☐ Key-type mode switch	
☐ Ground fault module	
□ Auxiliary relays (3)	
☐ Echelon LonWorks interface	

- $\hfill\square$ Modion Gateway to convert to Modbus (loose)
- □ PowerCommand iWatch web server for remote monitoring and alarm notification (loose)
- ☐ Digital input and output module(s) (loose)
- ☐ Remote annunciator (loose)
- □ Paralleling
- □ Power transfer control

For further detail see document S-1444.

Our energy working for you.™





Ratings definitions

Emergency standby power (ESP):

Applicable for supplying power to varying electrical load for the duration of power interruption of a reliable utility source. Emergency Standby Power (ESP) is in accordance with ISO 8528. Fuel Stop power in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.

Limited-time running power (LTP):


Applicable for supplying power to a constant electrical load for limited hours. Limited Time Running Power (LTP) is in accordance with ISO 8528.


Prime power (PRP):

Applicable for supplying power to varying electrical load for unlimited hours. Prime Power (PRP) is in accordance with ISO 8528. Ten percent overload capability is available in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.

Base load (continuous) power (COP):

Applicable for supplying power continuously to a constant electrical load for unlimited hours. Continuous Power (COP) in accordance with ISO 8528, ISO 3046, AS 2789, DIN 6271 and BS 5514.





This outline drawing is for reference only. See respective model data sheet for specific model outline drawing number.

Do not use for installation design

	Dim "A"	Dim "B"	Dim "C"	Set Weight*	Set Weight*
Model	mm (in.)	mm (in.)	mm (in.)	dry kg (lbs)	wet kg (lbs)
DQCA	4394.5 (173)	1715 (68)	2060.1 (81.1)	6377 (14061)	6518 (14372)
DQCB	4394.5 (173)	1715 (68)	2060.1 (81.1)	6377 (14061)	6518 (14372)
DQCC	4394.5 (173)	1715 (68)	2060.1 (81.1)	6377 (14061)	6518 (14372)

^{*} Note: Weights represent a set with standard features. See outline drawings for weights of other configurations.

Cummins Power Generation

1400 73rd Avenue N.E. Minneapolis, MN 55432 USA Telephone: 763 574 5000 Fax: 763 574 5298

Warning: Back feed to a utility system can cause electrocution and/or property damage. Do not connect to any building's electrical system except through an approved device or after building main switch is open.

Our energy working for you.™

www.cumminspower.com

