

Diesel generator set QSL9-G3/G5 series engine



> **Specification sheet**
220 kW - 300 kW standby

Our energy working for you.™



Description

Cummins Power Generation commercial generator sets are fully integrated power generation systems providing optimum performance, reliability and versatility for stationary standby and prime power applications. Codes or standards compliance may not be available with all model configurations – consult factory for availability.



This generator set is designed in facilities certified to ISO 9001 and manufactured in facilities certified to ISO 9001 or ISO 9002.



The Prototype Test Support (PTS) program verifies the performance integrity of the generator set design. Cummins Power Generation products bearing the PTS symbol meet the prototype test requirements of NFPA 110 for Level 1 systems.



All low voltage models are CSA certified to product class 4215-01.



The generator set is available listed to UL 2200, Stationary Engine Generator Assemblies for all 60 Hz low voltage models. The PowerCommand control is Listed to UL 508 - Category NITW7 for U.S. and Canadian usage.

U.S. EPA

Engine certified to Stationary Emergency U.S. EPA New Source Performance Standards, 40 CFR 60 subpart IIII Tier 3 exhaust emission levels (U.S. applications must be applied per this EPA regulation.) or exhaust emissions from the generator set meet levels formerly defined by U.S. EPA as Tier 1.

Features

Cummins® heavy-duty engine - Rugged 4-cycle, industrial diesel delivers reliable power, low emissions and fast response to load changes.

Alternator - Several alternator sizes offer selectable motor starting capability with low reactance 2/3 pitch windings, low waveform distortion with non-linear loads and fault clearing short-circuit capability.

Permanent magnet generator (PMG) - Offers enhanced motor starting and fault clearing short-circuit capability.

Control system - The PowerCommand® electronic control is standard equipment and provides total genset system integration including automatic remote starting/stopping, precise frequency and voltage regulation, alarm and status message display, AmpSentry™ protection, output metering, auto-shutdown at fault detection and NFPA 110 Level 1 compliance.

Cooling system - Standard cooling package provides reliable running at the rated power level.

Enclosures - Optional weather protective and sound attenuated enclosures are available.

Fuel tanks - Dual wall sub-base fuel tanks are also available.

NFPA - The genset accepts full rated load in a single step in accordance with NFPA 110 for Level 1 systems.

Warranty and service - Backed by a comprehensive warranty and worldwide distributor network.

Model	Standby rating		Prime rating		Continuous rating		Data sheets	
	60 Hz kW (kVA)	50 Hz kW (kVA)	60 Hz kW (kVA)	50 Hz kW (kVA)	60 Hz kW (kVA)	50 Hz kW (kVA)	60 Hz	50 Hz
DQDAA	250 (313)	220 (275)	225 (281)	200 (250)			D-3441, 3442	D-3445
DQDAB	275 (344)	250 (313)	250 (313)	227 (284)			D-3443	D-3446
DQDAC	300 (375)	265 (331)	270 (338)	240 (300)			D-3444	D-3447

Generator set specifications

Governor regulation class	ISO 8528 Part 1 Class G3
Voltage regulation, no load to full load	± 0.5%
Random voltage variation	± 0.5%
Frequency regulation	Isochronous
Random frequency variation	± 0.5%
Radio frequency emissions compliance	IEC 801.2 through IEC 801.5; MIL-STD-461C, Part 9

Engine specifications

Bore	114.0 mm (4.49 in)
Stroke	119.1 mm (4.69 in)
Displacement	8.9 L (543 in ³)
Configuration	Cast iron, in-line 6 cylinder
Battery capacity	750 amps minimum at ambient temperature of -12 °C (10 °F) and above
Battery charging alternator	70 amps
Starting voltage	24 volt, negative ground
Fuel system	Direct injection: number 2 diesel fuel, fuel filter (with water separator), automatic electric fuel shutoff
Fuel filter	
Air cleaner type	
Lube oil filter type(s)	Single spin-on, combination full flow and bypass filters
Standard cooling system	High ambient radiator

Alternator specifications

Design	Brushless, 4 pole, drip proof revolving field
Stator	2/3 pitch
Rotor	Single bearing, flexible discs
Insulation system	Class H
Standard temperature rise	125 °C standby, 105 °C prime
Exciter type	PMG (Permanent magnet generator)
Phase rotation	A (U), B (V), C (W)
Alternator cooling	Direct drive centrifugal blower
AC waveform total harmonic distortion	< 5% no load to full linear load, < 3% for any single harmonic
Telephone influence factor (TIF)	< 50 per NEMA MG1-22.43
Telephone harmonic factor (THF)	< 3

Available voltages

60 Hz 3-phase			50 Hz 3-phase			
Reconnectable			Non-Reconnectable	Reconnectable		Non-Reconnectable
• 110/190	• 120/208	• 127/220	• 277/480	• 110/190	• 120/208	• 127/220
• 139/240	• 120/240	• 220/380	• 347/600	• 139/240	• 120/240	• 220/380
• 240/416	• 254/440	• 277/480		• 240/416	• 254/440	• 277/480

Note: Consult factory for other voltages.

Generator set options and accessories

Engine <input type="checkbox"/> 120/240 V 1500 W coolant heater <input type="checkbox"/> 120/240 V 150 W lube oil heater <input type="checkbox"/> Heavy duty air cleaner <input type="checkbox"/> Engine oil temperature Control panel <input type="checkbox"/> 120/240 V 100 W control anti-condensation heater <input type="checkbox"/> Exhaust pyrometer <input type="checkbox"/> Ground fault indication <input type="checkbox"/> Remote fault signal package <input type="checkbox"/> Run relay package <input type="checkbox"/> Paralleling configuration	Alternator <input type="checkbox"/> 80 °C rise <input type="checkbox"/> 105 °C rise <input type="checkbox"/> 125 °C rise <input type="checkbox"/> 120/240 V 100 W anti-condensation heater <input type="checkbox"/> PMG excitation <input type="checkbox"/> Single phase Exhaust system <input type="checkbox"/> Genset mounted muffler <input type="checkbox"/> Heavy duty exhaust elbow <input type="checkbox"/> Slip on exhaust connection <input type="checkbox"/> NPT exhaust connection	Cooling system <input type="checkbox"/> 50 °C ambient Fuel system <input type="checkbox"/> 12 hour sub-base tank (dual wall) <input type="checkbox"/> 24 hour sub-base tank (dual wall) <input type="checkbox"/> 473 L (125 gal) sub-base tank (single wall) Generator set <input type="checkbox"/> AC entrance box <input type="checkbox"/> Battery <input type="checkbox"/> Battery charger	<input type="checkbox"/> Export box packaging <input type="checkbox"/> UL 2200 Listed <input type="checkbox"/> Main line circuit breaker <input type="checkbox"/> PowerCommand Network Communications Module (NCM) <input type="checkbox"/> Remote annunciator panel <input type="checkbox"/> Spring isolators <input type="checkbox"/> Enclosure: aluminum, steel, weather protective or sound attenuated <input type="checkbox"/> 2 year standby power warranty <input type="checkbox"/> 2 year prime power warranty <input type="checkbox"/> 5 year basic power warranty <input type="checkbox"/> 10 year major components warranty
--	--	---	--

Note: Some options may not be available on all models - consult factory for availability.

Our energy working for you.™

www.cumminspower.com

©2011 Cummins Power Generation Inc. All rights reserved. Cummins Power Generation and Cummins are registered trademarks of Cummins Inc. PowerCommand, AmpSentry InPower and "Our energy working for you." are trademarks of Cummins Power Generation. Other company, product or service names may be trademarks or service marks of others. Specifications are subject to change without notice.
S-1585c (6/11)



Control system PCC 2100



- PowerCommand control** is an integrated generator set control system providing governing, voltage regulation, engine protection and operator interface functions. Major features include:
- Integral AmpSentry™ Protective Relay providing a full range of alternator protection functions that are matched to the alternator provided.
 - Battery monitoring and testing features and smart starting control system.
 - Three phase sensing, full wave rectified voltage regulation system, with a PWM output for stable operation with all load types.
 - Standard PCCNet™ and optional Echelon® LonWorks® network interface.
 - Control suitable for operation in ambient temperatures from -40 °C to +70 °C (-40 °F to +158 °F) and altitudes to 5000 meters (13,000 feet).
 - Prototype tested; UL, CSA, and CE compliant.
 - InPower™ PC-based service tool available for detailed diagnostics.

Operator/display panel

- Off/manual/auto mode switch
- Manual run/stop switch
- Panel lamp test switch
- Emergency stop switch
- Alpha-numeric display with pushbutton access for viewing engine and alternator data and providing setup, controls and adjustments
- LED lamps indicating genset running, not in auto, common warning, common shutdown
- Configurable LED lamps (5)
- Configurable for local language

Engine protection

- Overspeed shut down
- Low oil pressure warning and shut down
- High coolant temperature warning and shut down
- High oil temperature warning (some models)
- Low coolant level warning or shut down
- Low coolant temperature warning
- High and low battery voltage warning
- Weak battery warning
- Dead battery shut down
- Fail to start (overcrank) shut down
- Fail to crank shut down
- Redundant -start disconnect
- Cranking lockout
- Sensor failure indication

Engine data

- DC voltage
- Lube oil pressure
- Coolant temperature
- Lube oil temperature (some models)
- Engine speed

AmpSentry AC protection

- Over current and short-circuit shut down
- Over current warning
- Single and three phase fault regulation
- Over and under voltage shut down
- Over and under frequency shut down
- Overload warning with alarm contact
- Reverse power and reverse Var shut down
- Excitation fault

Alternator data

- Line-to-line and line-to-neutral AC volts
- Three phase AC current
- Frequency
- Total and individual phase power factor, kW and kVA

Other data

- Genset model data
- Start attempts, starts, running hours
- kW hours (total and since reset)
- Fault history
- Load profile (hours less than 30% and hours more than 90% load)
- System data display (optional with network and other PowerCommand gensets or transfer switches)

Governing

- Digital electronic isochronous governor
- Temperature dynamic governing
- Smart idle speed mode
- Glow plug control (some models)

Voltage regulation

- Digital PWM electronic voltage regulation
- Three phase line-to-neutral sensing
- Suitable for PMG or shunt excitation
- Single and three phase fault regulation
- Configurable torque matching

Control functions

- Data logging on faults
- Fault simulation (requires InPower)
- Time delay start and cooldown
- Cycle cranking
- PCCNet interface
- Configurable customer inputs (4)
- Configurable customer outputs (4)
- Configurable network inputs (8) and outputs (16) (with optional network)
- Remote emergency stop

Options

- LED bargraph AC data display
- Thermostatically controlled space heater
- Key-type mode switch
- Ground fault module
- Auxiliary relays (3)
- Echelon LONWORKS interface
- Modicon Gateway to convert to Modbus (loose)
- PowerCommand iWatch web server for remote monitoring and alarm notification (loose)
- Digital input and output module(s) (loose)
- Remote annunciator (loose)

For further detail see document S-1409.

Our energy working for you.™

www.cumminspower.com

©2011 Cummins Power Generation Inc. All rights reserved. Cummins Power Generation and Cummins are registered trademarks of Cummins Inc. PowerCommand, AmpSentry InPower and "Our energy working for you." are trademarks of Cummins Power Generation. Other company, product or service names may be trademarks or service marks of others. Specifications are subject to change without notice.
S-1585c (6/11)



Ratings definitions

Emergency standby power (ESP):

Applicable for supplying power to varying electrical load for the duration of power interruption of a reliable utility source. Emergency Standby Power (ESP) is in accordance with ISO 8528. Fuel Stop power in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.

Limited-time running power (LTP):



Applicable for supplying power to a constant electrical load for limited hours. Limited Time Running Power (LTP) is in accordance with ISO 8528.

Prime power (PRP):

Applicable for supplying power to varying electrical load for unlimited hours. Prime Power (PRP) is in accordance with ISO 8528. Ten percent overload capability is available in accordance with ISO 3046, AS 2789, DIN 6271 and BS 5514.

Base load (continuous) power (COP):

Applicable for supplying power continuously to a constant electrical load for unlimited hours. Continuous Power (COP) in accordance with ISO 8528, ISO 3046, AS 2789, DIN 6271 and BS 5514.



This outline drawing is for reference only. See respective model data sheet for specific model outline drawing number.

Do not use for installation design

Model	Dim "A" mm (in.)	Dim "B" mm (in.)	Dim "C" mm (in.)	Set Weight* dry kg (lbs)	Set Weight* wet kg (lbs)
DQDAA	3023 (119.0)	1270 (50.0)	1676 (66.0)	2184 (4814)	2234 (4926)
DQDAB	3023 (119.0)	1270 (50.0)	1676 (66.0)	2184 (4814)	2234 (4926)
DQDAC	3023 (119.0)	1270 (50.0)	1676 (66.0)	2319 (5113)	2370 (5225)

* Weights represent a set with standard features. See outline drawings for weights of other configurations.

Cummins Power Generation

1400 73rd Avenue N.E.
Minneapolis, MN 55432 USA
Telephone: 763 574 5000
Fax: 763 574 5298

Warning: Back feed to a utility system can cause electrocution and/or property damage. Do not connect to any building's electrical system except through an approved device or after building main switch is open.

Our energy working for you.™

www.cumminspower.com

©2011 Cummins Power Generation Inc. All rights reserved. Cummins Power Generation and Cummins are registered trademarks of Cummins Inc. PowerCommand, AmpSentry InPower and "Our energy working for you." are trademarks of Cummins Power Generation. Other company, product or service names may be trademarks or service marks of others. Specifications are subject to change without notice.
S-1585c (6/11)

