

Rental Power 500 kW



Description

This Cummins Power Generation rental package is a fully integrated mobile power generation system, providing optimum performance, reliability, and versatility for standby and prime power applications.

The package utilizes custom designed switchgear to meet severe customer requirements. This switchgear provides reconnectable voltage via a link board design, automatic start/stop control and easy connection to existing installations.

Features

Cummins diesel engines

- Rugged 4-cycle industrial diesel delivers reliable power and fast response to load changes.
- Lightweight, compact, and excellent fuel economy.
- Equipped with heavy duty air cleaners, bypass-type oil filters, and dual-element fuel/water separation filtration system with 4-way valve.
- Includes jacket water heaters for more reliable operation in emergency standby applications.

Control system

- The most advanced, reliable, and capable generator set control system available in the market today.
- Integrated generator set governing, voltage regulation, protection, in one easy-to-operate customer interface.
- Remote monitoring and operation ready.
- Integrated ground fault indication.

Newage alternators

- Designed and built by Cummins Generator Technologies.
- Voltage reconnectable - 480/277 VAC high Wye to 208/120 VAC low Wye standard, 600 VAC optional.
- Alternators designed for improved motor starting.
- Permanent magnet excitation for improved performance in cyclic and non-linear load applications.

Rental package enclosure

- Designed for serviceability access.
- Optimized fuel capacity.
- Fluid containment design for greater environmental protection.
- Sound attenuated to minimize impact on local environment.
- Vertical cooling air and engine exhaust path to minimize sound level adjacent to the container.
- Equipped with 24 VDC lighting.
- Unit has paralleling capabilities at 480 and 600 VAC only.
- Utility grade breaker.
- Shore power 100 amp service breaker panel – single phase 120/240 VAC: (2) 30 amp breakers (one for each coolant heater) – 240 VAC: (26.75 amp = 6420 watts for the heater). (1) 15 amp breaker – 120 VAC (GFIs), (1) 15 amp breaker – 120 VAC (battery charger).

Options

Cold weather package (includes):

- Additional diesel fired block heater
- Battery heating pad
- Floor insulation
- Actuated louver control
- Transport Canada UN31A certified fuel tank

Model	Voltages (V)	Standby Rating		Prime Rating		Engine model	Alternator model	Generator* Specification Sheet (Ref)
		60 Hz kW (kVA)	50 Hz kW (kVA)	60 Hz kW (kVA)	50 Hz kW (kVA)			
C500D6RG	208/480	500 (625)		455 (569)		QSX15-G9	HC5F	S-1582
	600	500 (625)		455 (569)		QSX15-G9	HC5D	S-1582

* Not all reference data is applicable.

Our energy working for you.™

©2013 Cummins Power Generation Inc. | S-1279t (4/13)

cumminspower.com

Generator set specifications

Rated speed, rpm	1800- 60 Hz
Voltage regulation, no load to full load	±0.5%
Random voltage variation	±0.25%
Frequency regulation	Isochronous
Random frequency variation	±0.25%
Radio frequency interference	IEC 801.2, level 4 electrostatic discharge IEC 801.3, level 3 radiated susceptibility

Engine specifications

Engine model	QSX15-G9 NR
Engine data sheet	DS-10349
Tier rating	TPEM (Tier 2)
Design	Turbocharged with air-to-air charge air cooling, diesel fueled
Bore	136.9 mm (5.39 in.)
Stroke	168.9 mm (6.65 in.)
Displacement	14.9 liters (912 in ³)
Cylinder block	Cast iron, In-Line 6 cylinder with replaceable wet liners.
Battery capacity	2 x 12V 1235 CCA (Wired in series for 24V)
Battery charging alternator	35 amps
Starting voltage	24 volt, negative ground
Fuel system	Direct injection: number 2-D per ASTM D975 diesel fuel
Fuel filter	Spin on fuel filter with water separator
Air cleaner type	2-stage dry replaceable element with dust ejectors (qty: 2)
Lube oil filter type(s)	Single spin-on combination element with full flow and bypass filtration
Oil capacity	83.3 L (88 qt)
Standard cooling system	122 °F (50 °C) ambient radiator

Alternator specifications

Alternator data sheet	ADS-306 (600 VAC optional) ADS-308 (208/480 VAC)
Design	Brushless, 4-pole, drip-proof revolving field
Stator	2/3 pitch
Rotor	Direct-coupled by flexible disc
Insulation system	Class F per NEMA MG1-1.65 (208/480 VAC); class H per NEMA MG1-1.65 (600 VAC optional)
Standard temperature rise	105/40 °C standby (208/480 VAC), 125/40 °C standby (600 VAC optional)
Exciter type	Permanent magnet generator (PMG)
Phase rotation	A (U), B (V), C (W)
Alternator cooling	Direct-drive centrifugal blower
AC waveform total harmonic distortion	<5% total no load to full linear load <3% for any single harmonic
Telephone influence factor (TIF)	<50 per NEMA MG1-22.43
Telephone harmonic factor (THF)	<3

Power capability specifications

	Standby rating			
	240 V, 1 phase Amps	208 V, 3 phase Amps	480 V, 3 phase Amps	600 V, 3 phase Amps
C500D6RG		1737	753	602

Electrical power panel specifications

Model voltage	120 V duplex receptacles	240 V twist	Load lug connection (stud diameter)	Load lug circuit breakers
208/480 V	2 - 20 Amp		1/2 inch	1800 Amp
600 V	2 - 20 Amp		1/2 inch	800 Amp

Site derating factors

Genset may be operated up to 640 m (2100 ft) and 50°C (122°F) without power deration. For sustained operation above these conditions up to 1150 m (3770 ft), derate by 3.8% per 305 m (1000 ft), and 6.1% per 10°C (3.4% per 10°F). Above 1150 m (3770 ft) up to 1680 m (5510 ft), derate 6.3% total for 1150 m (3770 ft) plus 1.6% per 305 m (1000 ft) over 1150 m (3770 ft) and 3.8% per 10°C (2.2% per 10°F). Above 1680 m (5510 ft) up to 3000 m (9840 ft), derate 9% total for 1680 m (5510 ft) plus 3.7% per 305 m (1000 ft) and 5.7% per 10°C (3.2% per 10°F). Above 3000 m (9840 ft), derate 24.8% total for 3000 m (9840 ft) plus 1.8% per 305 m (1000 ft) above 3000 m (9840 ft) and 10% per 10°C (5.6% per 10°F).

Our energy working for you.™

©2013 Cummins Power Generation Inc. | S-1279t (4/13)

cumminspower.com

Control system

PowerCommand control with AmpSentry™ protection

- Integrated automatic voltage regulator and engine speed governor
- AmpSentry protection guards the electrical integrity of the alternator and power system from the effects of overcurrent, over/under voltage, under frequency and overload conditions
- Control components designed to withstand the vibration levels typical in generator sets

Standard Control Description

- Analog % of current meter (amps)
- Analog AC frequency meter
- Analog AC voltage meter
- Analog % of load meter (kW)
- Cycle cranking control
- Digital display panel
- Emergency stop switch
- Idle mode control
- Menu switch
- Panel backlighting
- Remote starting, 12 volt, 2 wire
- Reset switch
- Run-off-auto switch
- Sealed front panel, gasketed door
- Self diagnostics
- Voltmeter/ammeter phase selector switch

Standard Performance Data Warnings

- High coolant Temperature
- High DC voltage
- Low coolant temperature
- Low DC voltage
- Low oil pressure
- Over current
- Overload load shed contacts
- Up to four customer fault inputs
- Weak battery
- Overflow
- Overspeed
- Short circuit
- Underfrequency

Standard protection functions

- Voltmeter/ammeter phase selector
- Warnings
- High coolant temperature
- High DC voltage
- Low coolant temperature
- Low DC voltage
- Low oil pressure
- Over current
- Overload load shed contacts
- Up to four customer fault inputs
- Weak battery
- Overflow

Shutdowns

- Emergency stop
- Fail to crank
- High AC voltage
- High coolant temperature
- Low coolant level
- Low AC voltage
- Low oil pressure
- Overcurrent
- Overspeed
- Short circuit
- Underfrequency



Optional Features Shown


Ratings definitions

Standby:

Applicable for supplying emergency power for the duration of normal power interruption. No sustained overload capability is available for this rating. (Equivalent to Fuel Stop Power in accordance with ISO3046, AS2789, DIN6271 and BS5514). Nominally rated.

Prime (unlimited running time):

Applicable for supplying power in lieu of commercially purchased power. Prime power is the maximum power available at a variable load for an unlimited number of hours. A 10% overload capability is available for limited time. (Equivalent to Prime Power in accordance with ISO8528 and Overload Power in accordance with ISO3046, AS2789, DIN6271, and BS5514). This rating is not applicable to all generator set models.



Dimensions

Model	Dim "A" mm (in.)	Dim "B" mm (in.)	Dim "C" mm (in.)	Weight w/o fuel kg (lbs)	Weight with fuel kg (lbs)	Fuel capacity liters (gal)
C500D6RG	6071 (239)	2438 (96)	2591 (102)	10324 (22760)	13018 (28700)	3214 (849)
With chassis	6071 (239)	2438 (96)	3759 (148)	13354 (29440)	16048 (35380)	3214 (849)

Note: Optional cold weather package adds 1733 kg (3820 lbs) weight and uses 30 ft. container.

Optional Transport Canada fuel tank capacity 1300 gal. Available with 30 ft. container only.

Fuel consumption

60 Hz Ratings, kW (kVA)	Load	Standby 500 (625)				Prime 455 (569)			
		¼	½	¾	Full	¼	½	¾	Full
	US Gal/hr	11.6	18.8	25.7	34.4	10.9	17.6	23.7	30.4
	L/hr	44	71	97	130	41	67	90	115

Specifications

Model	KW rating		Sound level at full load dB(A) @ 7 m	Tier rating	Hours of operation (75% load)	
	Standby	Prime			Standby	Prime
C500D6RG	500	455	72	TPEM (Tier II)	33	35
					With Transport Canada fuel tank	
					50	54

Accessories

	Part Number
20 ft. Air Ride Chassis (standard package only)	0410-1378
30 ft. air Ride Chassis (cold weather package only)	0410-1379
Access Ladder*	0410-1371
Folding Ladder	0410-1362

* One access ladder provided with purchase of unit

Warranty

All components and subsystems are covered by an express limited one-year warranty.

Codes and standards

 <p>This generator set is designed in facilities certified to ISO 9001 and manufactured in facilities certified to ISO 9001 or ISO 9002.</p>	 <p>All low voltage models are CSA certified to product class 4215-01.</p>
 <p>The Prototype Test Support (PTS) program verifies the performance integrity of the generator set design. Cummins Power Generation products bearing the PTS symbol meet the prototype test requirements of NFPA 110 for Level 1 systems.</p>	 <p>Engine previously certified to U.S. EPA Nonroad Source Emissions Standards, 40 CFR 89, Tier 2. The engine used in this generator set may be used in mobile applications in accordance with the EPA Transition Program for Equipment Manufacturers (TPEM); this provision has specific limitations (see 40 CFR, 1039.625).</p>

North America
1400 73rd Avenue N.E.
Minneapolis, MN 55432
USA

Phone 763 574 5000
Fax 763 574 5298

Our energy working for you.™

©2013 Cummins Power Generation Inc. All rights reserved.

Cummins Power Generation and Cummins are registered trademarks of Cummins Inc. PowerCommand, AmpSentry, InPower and "Our energy working for you." are trademarks of Cummins Power Generation. Other company, product, or service names may be trademarks or service marks of others. Specifications are subject to change without notice.

S-1279t (4/13)



cumminspower.com